



### Statie D – Dimensiuni standard scule fante aerisire (LOUVRE)

- a)  $A = 50,8\text{mm} / B = 12,7\text{mm} / C = 4,75\text{mm} / D = 19,05\text{mm}$
- b)  $A = 63,5\text{mm} / B = 12,7\text{mm} / C = 4,75\text{mm} / D = 19,05\text{mm}$
- c)  $A = 76,2\text{mm} / B = 15,88\text{mm} / C = 6,35\text{mm} / D = 23,81\text{mm}$
- d)  $A = 88,9\text{mm} / B = 15,88\text{mm} / C = 6,35\text{mm} / D = 23,81\text{mm}$

### Statie E – Dimensiuni standard scule fante aerisire (LOUVRE)

- a)  $A = 50,8\text{mm} / B = 12,7\text{mm} / C = 4,75\text{mm} / D = 19,05\text{mm}$
- b)  $A = 63,5\text{mm} / B = 12,7\text{mm} / C = 4,75\text{mm} / D = 19,05\text{mm}$
- c)  $A = 76,2\text{mm} / B = 15,88\text{mm} / C = 6,35\text{mm} / D = 23,81\text{mm}$
- d)  $A = 88,9\text{mm} / B = 15,88\text{mm} / C = 6,35\text{mm} / D = 23,81\text{mm}$
- e)  $A = 101,6\text{mm} / B = 19,05\text{mm} / C = 6,35\text{mm} / D = 28,58\text{mm}$
- f)  $A = 114,3\text{mm} / B = 19,05\text{mm} / C = 6,35\text{mm} / D = 28,58\text{mm}$